

2G Handheld XRF Analyzers

ATX2600

Feature

- Elements Mg~U or Ti~U
- Alloy grade L >2000, free library > 300 , self-building library, SS, Alloy steel, Tool steel grade ID and contents, percentage, including common several hundreds of SS201, SS203, SS301, SS304, SS316, SS321
- Copper alloy grade and contents, including brass, bronze, copper, pure copper
- Various alloy including alloy of Ti, Sn, Lead, Zn, Tungsten, Al, Ni
- Precious metal of Gold, Ag, Platinum, Rhodium, Pd.
- Sample state of solid, powder and sheet
- Good reliability and detect limit <0.01%ppm

Application

- NDT, Fast, Accuracy alloy elements ID and grades ID
- Metal ID/ Scrap Metal Sorting
- QA/QC manufacturing
- Pharmaceutical and biological medicine
- Positive materials ID, oil refining, petrification
- Thermo/Water/Nuclear power plant
- Raw materials PMI ID

Description

Optosky ATX2600 is self-designed second generation handheld X-ray fluorescence spectroscopy analyzer.

Optosky is the most affordable handheld XRF analyzer manufacturer for fast, accurate, and reliable XRF spectrometer, With the rugged and compact size, the fastest identification of alloy, precious metals, mining.

With advantage of SDD Elements Mg~U or Si-Pin Ti~U, Alloy grade >2000, free library> 300 entries, self-building library, SS, Alloy steel, Tool steel grade identification and contents, percentage, including common several hundreds of SS201, SS203, SS301, SS304, SS316, SS321 etc

Copper alloy steel grade , contents , say brass, bronze, copper, pure copper etc

Various alloy of Ti , Sn, Lead, Zn, Tungsten, Al, Ni
Precious metal of Gold, Ag, Platinum, Rhodium, Pd.



1. Parameters

Item	Description
Weight	Body: 1.4kg plus battery 0.1kg, Total Weight: 1.5Kg
Dimension	300x 90x 220 mm
Target Material	Au, Ag, W, Ta, Pd
Voltage current and power	Si-pin: 35kV SDD: 50KV
Detector	Si-Pin or SDD
Temperature	-35~85 degree
Data interface	Bluetooth, USB
IP Level	IP65
Resolution	<180ev
Power	2 batery
Software	Windows, WIFI,8G memory card,>100,000 database
Touch screen	3.5 inch touch screen
Elements	Si-Pin: Element Ti~U, including Ni, Cu, Zn, Hf, Ta, W, Se, Ru, Hg, Bi, Pb, Zr, Sb, Sn, Ag, Cd, Mo, Nb, Re, Br, Pd, Rh, Pt, Au, Ir, As SDD: Element Mg~U, eg Mg, Al, Si, P, S, Ti, Cr, Fe, Mn, V, Co , Ni, Cu, Zn, Hf, Ta, W, Se, Ru, Hg, Bi, Pb, Zr, Sb, Sn, Ag, Cd, Mo, Nb, Re, Br, Pd, Rh, Pt, Au, Ir, As
Radiation	<2.5 μ Sv/h Complaint with EU radiation protectipon regulation
Elements contents	0.01% ~ 99.99%

2. Reliability and Accuracy

Metal detect limit <0.01%

- A. detect content > 5%, stabilized readout error $\pm 0.1 \sim 0.2\%$
- B. detect content 0.5~5%, stabilized readout error $\pm 0.05\% \sim 0.1\%$
- C. detect content 0.1~0.5%, stabilized readout error $\pm 0.01 \sim 0.03\%$
- D. detect content 0.1%, stabilized readout error $\pm 10 \sim 15\%$

3. Attachments

S/N	Description	QTY
1	XRF Analyzer	1
2	Free Software	1
3	Li Battery	2
4	Charger	1
5	USB Wire	1
6	316 SS sample	1
7	User Manual	1
8	QC Report	1

9	Window Protect Film	1
10	Carrying Case	1

Free Library				
Fe-based Alloy			Ni-based Alloy	
201	Alnico VIII	Tool Steel	Ni	Inco 718
203	AL6XN		80-20	Inco 722
301	AMS 350	A2	B-1900	Inco 738
304	AMS 355	A6	B-1900 Hf	Inco 750
309	CD4MCU	A7	Inco 617	Inco 792
310	Custom 450	A10	Inco 625	Inco 800
316	Custom 455	D2, D4	C-1023	Inco 801
317	Duplex 2205	D7	GMR 235	Inco 825
321	Elgiloy	H12	GTD 222	Inco 901
329	Ferallium 255	H13	Hast B	Inco 903
330	Greek Ascology	L6	Hast B2	Inco 909
347	Hy Mu 80	01	Hast C -4	Mar M 002
410/416/420	Kovar	06	Hast C -22	Mar M 200
410 Cb	Invar 36	07	Hast C -276	Mar M 246
422	Maraging C200	M1	Hast C -2000	Mar M 247
430/440	Maraging C250	M2	Hast F	Mar M 421
431	Maraging C300	M42	Hast G	Monel 400
434	Maraging C350	M4	Hast G-2	Monel 411
441	N 155	S1	Hast G-3	Monel 500

446	Ni-hard #1	S7	Hast G-30	MP35N
12L14	Ni-hard #4	T1	Hast N	Mu Metal
13-8Mo	Nitronic 40	Low alloy	Hast R	Nichrome V
15. 5 PH	Nitronic 50		Hast S	Nickel 200
17-4 PH	Nitronic 60		Hast X	Nim 101
19-9DL	RA333	铬钼钢	Hast W	Nim 263
19-9DX	RA330		Haynes 25	Nimonic 75
20Cb3		Carbon steel	Haynes 36	Nimonic 80A
20Mo4		1 1-4 Cr	Haynes 214	Nimonic 90
20Mo6		12L14	Haynes 230	Ni-Span 902
25-4-4		13-8 Mo	Haynes 188	Rene 41
254SMO		15-5 PH	Haynes 556	Rene 77
21-6-9		17-4 PH	HR-160	Rene 80
26-1		19-9DL	IN 100	Rene 95
29-4			Inco 600	Rene 125
29-4-2			Inco 601	Super therm
904 L			Nim 101	Udimet 500
A 286			Nim 263	Udimet 520
Alloy 42			Inco 690	Waspaloy
Alloy 49			Inco 702	
Alnico II			Inco 706	
Alnico V			Inco 713	
Free Library				
Co-based Alloy	Cu-based Alloy	Ti-based Alloy	Hybrid Alloy	Al-based Alloy

Co	Cu	Ti 10-2-3	97-3	AL-1100
F-75	70-30	Ti 13-11-13	Cb 103	AL-2011
FSX 414	80-20	Ti 15-3-3-3	CP Ta	AL-2024
HS-1	90-10	Ti 3 2-5	Densalloy	AL-2098 or AL-2195
HS-4	CDA 110	Ti 5-2-5	Tungsten	AL-2219 or AL-2519
HS-6	CDA 314	Ti 5 Sn 2 1-2	Carbide	AL-2618
HS-12	CDA 360	Ti 6-2-1-1	Zir 702	AL-3003
HS-19	CDA 544	Ti 6-22-22	Zir 705	AL-319
HS-21	CDA 630	Ti 6-2-4-2	Zir caloy	AL-356
HS-25 (L605)	CDA 706	Ti 6-2-4-6	2, 4	AL-380
HS-31	CDA 836	Ti 6-4	Zr	AL-5052
Haynes 188	CDA 863	Ti 6-6-2		AL-5083
Jetalloy	CDA 875	Ti 8-1-1		AL-5086
Mar M 302	CDA 903	Ti Beta C		AL-6061
Mar M 509	CDA 932	Ti-17		AL-6063
MP 35N	CDA 937	Ti-8		AL-6262
Star J	CDA 954	Ti 6-2-1-1		AL-7039
Ultimet	CDA 955			AL-7050
	CDA 8932			AL-7072
				AL-7075
				AL-7149